



IPR-12

Induced Polarization

IPR-12 SPECIFICATIONS

The IPR-12 IP receiver has been successfully used for many years as a mineral exploration tool, specifically for gold exploration.

Induced polarization can also be used as a method for mapping hydrocarbon plumes and geotechnical applications.

Inputs:	1 to 8 dipoles are measured simultaneously.
Input Impedance:	16 M Ω
SP Bucking:	\pm 10 volt range. Automatic linear correction operating on a cycle by cycle basis.
Input Voltage (Vp) Range:	50 μ V to 14 V
Chargeability (M) Range:	0 to 300 mV/V
Tau Range:	60 microseconds to 2000 seconds.
Reading Resolution of Vp, SP and M:	Vp - 10 μ V; SP - 1 mV; M - 0.01 mV/V
Absolute Accuracy of Vp, Sp and M:	Better than 1%
Common Mode Rejection:	At input more than 100dB.
Vp Integration Time:	10% to 80% of the current on time.
IP Transient Program:	Pulse selectable at 1,2,4,8,16 or 32 seconds. Programmable windows also available. 50% duty cycle.
Transmitter Timing:	On/off times of 1,2,4,8,16 or 32 seconds.
External Circuit Test:	All dipoles measured individually in sequence. Range 0 to 2 M Ω with 0.1 k Ω resolution. Circuit resistances displayed and recorded.
Filtering:	RF filter, 10 Hz 6 pole low pass filter, statistical noise spike removal.
Internal Test Generator:	1200 mV of SP; 807 mV of Vp and 30.28 mV/V of M.
Analog Meter:	For monitoring input signals; switchable to any dipole via keyboard.
Memory Capacity:	Stores approximately 400 dipoles of information when 8 dipoles are measured simultaneously.
Power Supply:	Rechargeable Ni-Cad D cells. More than 20 hours service at +25°C. (77°F), more than 8 hours at -30°C (-22°F)
Operating Temperature:	-30°C to +50°C (-22°F to 122°F)
Dimensions and Weights:	Console: 355 x 270 x 165 mm (14" x 10.6" x 6.5") Charger: 120 x 95 x 55 mm (4.7" x 3.7" x 2") Console: 5.8 kg (12.8 lbs.) Batteries: 1.3 kg (2.8 lbs.) Charger: 1.1 kg (2.4 lbs.)

OPTIONS

Transmitters
Software Packages
Training Program

ISO 9001:2000 registered company. All specifications are subject to change without notice.

Specification Sheet Part Number 745711 Revision 0



CANADA

Scintrex
222 Snidercroft Road
Concord, Ontario L4K 2K1
Telephone: +1 905 669 2280
Fax: +1 905 669 6403
e-mail: scintrex@scintrexltd.com
Website: www.scintrex.com



USA

Micro-g LaCoste
1401 Horizon Avenue
Lafayette, CO 80026
Telephone: +1 303 828 3499
Fax: +1 303 828 3288
e-mail: info@microglacoste.com
Website: www.microglacoste.com